

# 1PU10MC40 Cut Sheet



NITRA pneumatic coiled tubing, ether-based polyurethane, clear blue, 10mm outside diameter, 6.5mm inside diameter, 40 coils, 14.2ft (4.33m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1PU10MC40>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Coiled tubing
<b>Working Fluid</b>	Air or inert gas
<b>Material</b>	Ether-based polyurethane
<b>Color</b>	Clear blue
<b>Outside Diameter</b>	10mm
<b>Inside Diameter</b>	6.5mm
<b>Number of Coils</b>	40
<b>Working Length</b>	14.2ft (4.33m) working length
<b>Operating Pressure</b>	150 psi
<b>Operating Temperature</b>	-40 to +160 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>