

1PU14C10 Cut Sheet



NITRA pneumatic coiled tubing, ether-based polyurethane, clear blue, 1/4in outside diameter, 0.156in inside diameter, 10 coils, 3.2ft (0.98m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1PU14C10>

Technical Specifications

Brand	NITRA
Item	Coiled tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Clear blue
Outside Diameter	1/4in
Inside Diameter	0.156in
Number of Coils	10
Working Length	3.2ft (0.98m) working length
Operating Pressure	180 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document