

1UHD722918FTC Cut Sheet



Hammond disconnect enclosure, NEMA 12, right flange, 72 x 29 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1UHD722918FTC>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	12
IP Rating	IP54
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	72 x 29 x 18in (HxWxD)
Enclosure Height	72.13in
Enclosure Width	28.75in
Enclosure Depth	19.35in
Mounting	Freestanding
Dual Access	No
Knockouts	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Lift-off hinges
Number of Hinges Per Door	3
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document