

1/2PFX-72IN-FJXEE Cut Sheet



Gates ProFlex petroleum based hydraulic fluid hose assembly, synthetic rubber, braided steel wire reinforced, black, 1/2in inside diameter, 0.81in outside diameter, (2) -8 female straight JIC 37 deg fittings, 6ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1/2PFX-72IN-FJXEE>

Technical Specifications

| | |
|------------------------|---------------------------------|
| Brand | Gates |
| Item | Hose assembly |
| Series | ProFlex |
| Working Fluid | Petroleum based hydraulic fluid |
| Material | Synthetic rubber |
| Reinforcement | Braided steel wire |
| Color | Black |
| Inside Diameter | 1/2in |

| | |
|------------------------------|--|
| Outside Diameter | 0.81in |
| Connection | (2) -8 female straight JIC 37 deg fittings |
| Minimum Bend Radius | 3.5in |
| Working Length | 6ft working length |
| Operating Pressure | 4000 psi |
| Operating Temperature | -40 to +212 deg F |
| Duty Rating | 200,000 cycles |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |