

202852 Cut Sheet



di-soric patch cable signal converter, 4-pin M12 axial female to 3-pin M12 axial male, PNP to NPN, 10-35 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/202852>

Technical Specifications

Brand	di-soric
Item	Signal converter
Form Factor	Patch cable
Connector Type	4-pin M12 axial female to 3-pin M12 axial male
Function	PNP to NPN
Operating Voltage	10-35 VDC
Operating Temperature	-20 to +70 °C
Material	Plastic
Includes	Mounting hardware
Manufacturer Part Number	VKHM-Z/VSM-Z/U

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/202852.pdf>
See store item page for other formats.