

2030-12PZB Cut Sheet



igus bracket, 0.98in inside height, 1.5in inside width, 90 deg locking and 0 deg locking, polyamide, black. For use with 2400 and 2500 series energy chain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2030-12PZB>

Technical Specifications

| | |
|---------------|-----------------------------------|
| Brand | igus |
| Item | Bracket |
| Inside Height | 0.98in |
| Inside Width | 1.5in |
| Rotation Type | 90 deg locking and 0 deg locking |
| Material | Polyamide |
| Color | Black |
| For Use With | 2400 and 2500 series energy chain |

Agency Approvals

| | |
|-------------|---|
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2030-12PZB.pdf>
See store item page for other formats.