

20540067 Cut Sheet



WERMA Xenon tube industrial signal beacon, 58mm, clear/white, flashing strobe (0.75 Hz flash frequency), IP65, bracket mount, 115 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/20540067>

Technical Specifications

| | |
|-----------------------------|---|
| Brand | WERMA |
| Item | Industrial signal beacon |
| Bulb Type | Xenon tube |
| Operator Size | 58mm |
| Operator Color | Clear |
| Light Color(s) | Clear/white |
| Light Function | Flashing strobe (0.75 Hz flash frequency) |
| Housing Material | Polycarbonate |
| Mounting | Bracket |
| IP Rating | IP65 |
| Connection | Spring clamp |
| Touch to Acknowledge | No |
| Voltage Rating | 115 VAC |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/20540067.pdf>
See store item page for other formats.