

207-1332 Cut Sheet



WAGO 207 gel-filled splice enclosure, branch, IPX8, pre-filled silicone-free, serviceable, wet locations, outdoor and moisture-prone. Package of 4. For use with (2) 221-412, (1) 221-415, (3) 2773-402, (2) 2773-403, (1) 2773-405, (1) 2773-406, (1) 2773-408.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/207-1332>

Technical Specifications

Brand	WAGO
Series	207
Item	Gel-filled splice enclosure
Splice Type	Branch
Gel Type	Pre-filled silicone-free
Size	17.8 x 45.9 x 33.6mm (HxWxD)
Serviceable	Yes
Housing Material	Polypropylene
Housing Color	Gray

IP Rating	IPX8
Moisture Protection	Yes
Application	Wet locations, outdoor and moisture-prone
Max Wire Size	12 AWG
Quantity per Pack	4
For Use With	(2) 221-412, (1) 221-415, (3) 2773-402, (2) 2773-403, (1) 2773-405, (1) 2773-406, (1) 2773-408

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/207-1332.pdf>
See store item page for other formats.