

20840055 Cut Sheet



WERMA Xenon tube industrial signal beacon, 58mm, clear/white, flashing strobe (0.75 Hz flash frequency), IP65, 22.5mm panel mount, 24 VDC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/20840055>

Technical Specifications

| | |
|----------------------|---|
| Brand | WERMA |
| Item | Industrial signal beacon |
| Bulb Type | Xenon tube |
| Operator Size | 58mm |
| Operator Color | Clear |
| Light Color(s) | Clear/white |
| Light Function | Flashing strobe (0.75 Hz flash frequency) |
| IP Rating | IP65 |
| Mounting | 22.5mm panel |
| Touch to Acknowledge | No |
| Voltage Rating | 24 VDC |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |