

# 20840067 Cut Sheet



WERMA Xenon tube industrial signal beacon, 58mm, clear/white, flashing strobe (0.75 Hz flash frequency), IP65, 22.5mm panel mount, 115 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/20840067>

## Technical Specifications

|                             |   |
|-----------------------------|---|
| <b>Brand</b>                | WERMA                                     |
| <b>Item</b>                 | Industrial signal beacon                  |
| <b>Bulb Type</b>            | Xenon tube                                |
| <b>Operator Size</b>        | 58mm                                      |
| <b>Operator Color</b>       | Clear                                     |
| <b>Light Color(s)</b>       | Clear/white                               |
| <b>Light Function</b>       | Flashing strobe (0.75 Hz flash frequency) |
| <b>IP Rating</b>            | IP65                                      |
| <b>Mounting</b>             | 22.5mm panel                              |
| <b>Touch to Acknowledge</b> | No  |
| <b>Voltage Rating</b>       | 115 VAC                                   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E164155                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |