

211R2C36RD Cut Sheet



Megapro RATCHETING multi-bit screwdriver, 7 pieces, cushion grip with bit storage, 3.0in (75mm) shaft length, Phillips, Torx, square and slotted.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/211R2C36RD>

Technical Specifications

Brand	Megapro
Series	RATCHETING
Item	Screwdriver
Screwdriver Type	Multi-bit
Number of Pieces	7
Insulated	No
Overall Length	8.8in (224mm)
Shaft Length	3.0in (75mm)
Shaft Diameter	0.38in (9.7mm)

Handle Length	5.7in (145mm)
Handle Type	Cushion grip with bit storage
Tip Type	Phillips, Torx, square and slotted
Includes	(1) ratcheting handle with bit storage, (1) slotted bit (4, 6mm), (1) Phillips bit (#1, #2), (1) Phillips bit (#0, #3), (1) Torx bit (T10, T15), (1) Torx bit (T20, T25), (1) square bit (#1, #2)
Application	Screwdriving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document