

21324 Cut Sheet



Viking combination drill bit and machine tap set, 5 pieces, high-speed steel (HSS), 1/4in hex shank, UNC thread type, imperial, gold oxide finish, pouch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21324>

Technical Specifications

Brand	Viking	Point Cut	Split
Item	Combination drill bit and machine tap set	Shank Type	1/4in hex
Number of Pieces	5	Application	Thread making and hole cutting
Material	High-speed steel (HSS)	For Use On	Stainless steel, iron and steel
Thread Type	UNC	Measurement Type	Imperial
Thread	#6-32 UNC, #8-32 UNC, #10-24 UNC, #10-32 UNF and 1/4-20 UNC	Package Type	Pouch
Drill Bit Size	Wire number size 36, wire number size 29, wire number size 25, wire number size 21 and wire number size 7	Set Includes	Includes (5) combination drill bit and machine taps (#6-32 UNC, #8-32 UNC, #10-24 UNC, #10-32 UNF, 1/4-20 UNC), pouch
Finish	Gold oxide		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement