

21330 Cut Sheet



Viking combination drill bit and machine tap set, 6 pieces, high-speed steel (HSS), 3-flat shank, UNC thread type, imperial, gold oxide finish, pouch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21330>

Technical Specifications

Brand	Viking	Point Cut	Split
Item	Combination drill bit and machine tap set	Shank Type	3-flat
Number of Pieces	6	Application	Thread making and hole cutting
Material	High-speed steel (HSS)	For Use On	Stainless steel, iron and steel
Thread Type	UNC	Measurement Type	Imperial
Thread	#6-32 UNC, #8-32 UNC, #10-24 UNC, #10-32 UNF, #12-24 UNC and 1/4-20 UNC	Package Type	Pouch
Drill Bit Size	Wire number size 36, wire number size 29, wire number size 25, wire number size 21, wire number size 16 and wire number size 7	Set Includes	Includes (6) combination drill bit and machine taps (#6-32 UNC, #8-32 UNC, #10-24 UNC, #10-32 UNF, #12-24 UNC, 1/4-20 UNC), pouch
Finish	Gold oxide		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement