

# 214803 Cut Sheet

RUKO jobber-length drill bit, 3/32in, split point, high-speed steel (HSS), bright finish, round shank. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214803>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Drill bit
<b>Replacement</b>	No
<b>Drill Bit Type</b>	Jobber-length
<b>Drill Bit Size</b>	3/32in
<b>Material</b>	High-speed steel (HSS)
<b>Finish</b>	Bright
<b>Flute Angle</b>	25-30 degrees
<b>Flute Length</b>	1-1/4in
<b>Point Angle</b>	118 degrees
<b>Point Cut</b>	Split
<b>Shank Type</b>	Round
<b>Overall Length</b>	2.3in (58mm)
<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron
<b>Application</b>	Hole cutting
<b>Quantity per Pack</b>	10

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>