

214806 Cut Sheet



RUKO jobber-length drill bit, 9/64in, split point, high-speed steel (HSS), bright finish, round shank. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214806>

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Jobber-length
Drill Bit Size	9/64in
Material	High-speed steel (HSS)
Finish	Bright
Flute Angle	25-30 degrees
Flute Length	1-3/4in
Point Angle	118 degrees
Point Cut	Split
Shank Type	Round
Overall Length	2.9in (74mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting
Quantity per Pack	10

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document