


214810 Cut Sheet



RUKO jobber-length drill bit, 13/64in, split point, high-speed steel (HSS), bright finish, round shank. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214810>

Technical Specifications

| | |
|--------------------------|---|
| Brand | RUKO |
| Item | Drill bit |
| Replacement | No |
| Drill Bit Type | Jobber-length |
| Drill Bit Size | 13/64in |
| Material | High-speed steel (HSS) |
| Finish | Bright |
| Flute Angle | 25-30 degrees |
| Flute Length | 2-7/16in |
| Point Angle | 118 degrees |
| Point Cut | Split |
| Shank Type | Round |
| Overall Length | 3.6in (91mm) |
| For Use On | Aluminum, brass, plastic, steel, bronze and cast iron |
| Application | Hole cutting |
| Quantity per Pack | 10 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |