

# 214817 Cut Sheet



RUKO jobber-length drill bit, 5/16in, split point, high-speed steel (HSS), bright finish, round shank. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214817>

## Technical Specifications

|                |                        |
|----------------|------------------------|
| Brand          | RUKO                   |
| Item           | Drill bit              |
| Replacement    | No                     |
| Drill Bit Type | Jobber-length          |
| Drill Bit Size | 5/16in                 |
| Material       | High-speed steel (HSS) |
| Finish         | Bright                 |
| Flute Angle    | 25-30 degrees          |

|                   |   |
|-------------------|---|
| Flute Length      | 3-3/16in  |
| Point Angle       | 118 degrees   |
| Point Cut         | Split   |
| Shank Type        | Round   |
| Overall Length    | 4.5in (114mm)   |
| For Use On        | Aluminum, brass, plastic, steel, bronze and cast iron |
| Application       | Hole cutting  |
| Quantity per Pack | 10  |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/214817.pdf>  
See store item page for other formats.