

# 214850RO Cut Sheet



RUKO jobber-length drill bit set, 21 pieces, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214850RO>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Drill bit set
<b>Number of Pieces</b>	21
<b>Material</b>	High-speed steel (HSS)
<b>Drill Bit Type</b>	Jobber-length
<b>Drill Bit Size</b>	1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in and 3/8in
<b>Finish</b>	Bright
<b>Flute Angle</b>	25-30 degrees
<b>Point Angle</b>	118 degrees
<b>Point Cut</b>	Split
<b>Set Includes</b>	(21) bright finish HSS jobber length drill bits (1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 11/64, 3/16, 13/64, 7/32, 15/64, 1/4, 17/64, 9/32, 19/64, 5/16, 21/64, 11/32, 23/64 and 3/8in) and heavy-duty plastic case
<b>Application</b>	Hole cutting
<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>