

214851RO Cut Sheet



RUKO jobber-length drill bit set, 29 pieces, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214851RO>

Technical Specifications

Brand	RUKO
Item	Drill bit set
Number of Pieces	29
Material	High-speed steel (HSS)
Drill Bit Type	Jobber-length
Drill Bit Size	1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in and 1/2in
Finish	Bright
Flute Angle	25-30 degrees
Point Angle	118 degrees
Point Cut	Split
Set Includes	(29) bright finish HSS jobber length drill bits (1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 11/64, 3/16, 13/64, 7/32, 15/64, 1/4, 17/64, 9/32, 19/64, 5/16, 21/64, 11/32, 23/64, 3/8, 25/64, 13/32, 27/64, 7/16, 29/64, 15/32, 31/64 and 1/2in) and heavy-duty plastic case
Application	Hole cutting
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document