

214900R Cut Sheet



RUKO jobber-length drill bit, letter size R, split point, high-speed steel (HSS), bright finish, round shank. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/214900R>

Technical Specifications

Brand	RUKO	Flute Length	3-7/16in
Item	Drill bit	Point Angle	118 degrees
Replacement	No	Point Cut	Split
Drill Bit Type	Jobber-length	Shank Type	Round
Drill Bit Size	Letter size R	Overall Length	4.8in (122mm)
Material	High-speed steel (HSS)	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Finish	Bright	Application	Hole cutting
Flute Angle	20-30 degrees	Quantity per Pack	10

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document