

215115 Cut Sheet



RUKO jobber-length drill bit, 11.5mm, split point, 5% cobalt high-speed steel (HSSE-Co5), golden brown finish, round shank. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/215115>

Technical Specifications

Brand	RUKO	Point Angle	130 degrees
Item	Drill bit	Point Cut	Split
Replacement	No	Shank Type	Round
Drill Bit Type	Jobber-length	Overall Length	5.6in (141mm)
Drill Bit Size	11.5mm	For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Material	5% cobalt high-speed steel (HSSE-Co5)	Application	Hole cutting
Finish	Golden brown	Quantity per Pack	5
Flute Angle	36 degrees		
Flute Length	94mm		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document