

215120 Cut Sheet



RUKO jobber-length drill bit, 12mm, split point, 5% cobalt high-speed steel (HSSE-Co5), golden brown finish, round shank. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/215120>

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Jobber-length
Drill Bit Size	12mm
Material	5% cobalt high-speed steel (HSSE-Co5)
Finish	Golden brown
Flute Angle	36 degrees
Flute Length	101mm

Point Angle	130 degrees
Point Cut	Split
Shank Type	Round
Overall Length	5.9in (151mm)
For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Application	Hole cutting
Quantity per Pack	5

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document