

215125 Cut Sheet



RUKO jobber-length drill bit, 12.5mm, split point, 5% cobalt high-speed steel (HSSE-Co5), golden brown finish, round shank. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/215125>

Technical Specifications

| | |
|--------------------------|--|
| Brand | RUKO |
| Item | Drill bit |
| Replacement | No |
| Drill Bit Type | Jobber-length |
| Drill Bit Size | 12.5mm |
| Material | 5% cobalt high-speed steel (HSSE-Co5) |
| Finish | Golden brown |
| Flute Angle | 36 degrees |
| Flute Length | 101mm |
| Point Angle | 130 degrees |
| Point Cut | Split |
| Shank Type | Round |
| Overall Length | 5.9in (151mm) |
| For Use On | Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum |
| Application | Hole cutting |
| Quantity per Pack | 5 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |