

21514812055 Cut Sheet



Pfannenberg PYRA series LED traffic light, (2) tiers, red/green, selectable permanent, blinking or flashing light function, 12-48 VDC, colored lens, 172.4mm body length, light gray, direct mount, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21514812055>

Technical Specifications

Brand	Pfannenberg
Item	Traffic light
Bulb Type	LED
Series	PYRA
Number of Pre-Assembled Tiers	2
Light Color(s)	Red/green
Light Function	Selectable permanent, blinking or flashing
Voltage Rating	12-48 VDC

Lens Type	Colored
Body Length	172.4mm
Body Color	Light gray
Body Material	ABS plastic
Mounting	Direct
IP Rating	IP66
NEMA Rating	4/4X

Agency Approvals

UL Listed File #	E189090
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/21514812055.pdf>
See store item page for other formats.