

21555154055 Cut Sheet



Pfannenberg PYRA series Xenon tube audible-visual signal beacon, 101 dB at 1m, (8) selectable tone(s), selectable flashing strobe, amber, 166 x 114 x 134mm, 115 VAC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21555154055>

Technical Specifications

Brand	Pfannenberg	Material	ABS plastic
Item	Audible-visual signal beacon	Loudness Decibel	101 dB at 1m
Series	PYRA	Tone Frequency	110 Hz to 3 kHz
Bulb Type	Xenon tube	Tone Type	(8) selectable
Operator Size	166 x 114 x 134mm	Touch to Acknowledge	No
Operator Color	Amber	Voltage Rating	115 VAC
Light Color(s)	Amber	Mounting	Surface
Light Function	Selectable flashing strobe	IP Rating	IP66
Housing Material	Polycarbonate	NEMA Rating	4/4X

Agency Approvals

UL Listed File #	S7256
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/21555154055.pdf>
See store item page for other formats.