

21555814055 Cut Sheet



Pfannenberg PYRA series Xenon tube audible-visual signal beacon, 101 dB at 1m, (8) selectable tone(s), selectable flashing strobe, amber, 166 x 114 x 134mm, 10-57 VDC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21555814055>

Technical Specifications

| | |
|------------------|------------------------------|
| Brand | Pfannenberg |
| Item | Audible-visual signal beacon |
| Series | PYRA |
| Bulb Type | Xenon tube |
| Operator Size | 166 x 114 x 134mm |
| Operator Color | Amber |
| Light Color(s) | Amber |
| Light Function | Selectable flashing strobe |
| Housing Material | Polycarbonate |
| Material | ABS plastic |

| | |
|----------------------|-----------------|
| Loudness Decibel | 101 dB at 1m |
| Tone Frequency | 110 Hz to 3 kHz |
| Tone Type | (8) selectable |
| Touch to Acknowledge | No |
| Number of Alarms | 8 |
| Voltage Rating | 10-57 VDC |
| Mounting | Surface |
| IP Rating | IP66 |
| NEMA Rating | 4/4X |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | S7256 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/21555814055.pdf>
See store item page for other formats.