

21556818055 Cut Sheet



Pfannenberg PYRA series LED audible-visual signal beacon, 101 dB at 1m, (8) selectable tone(s), selectable permanent, blinking or flashing, red/yellow/green/blue, 166 x 114 x 134mm, 12-48 VDC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21556818055>

Technical Specifications

Brand	Pfannenberg
Item	Audible-visual signal beacon
Series	PYRA
Bulb Type	LED
Operator Size	166 x 114 x 134mm
Operator Color	Clear
Light Color(s)	Red/yellow/green/blue
Light Function	Selectable permanent, blinking or flashing
Housing Material	Polycarbonate
Material	ABS plastic

Loudness Decibel	101 dB at 1m
Tone Frequency	110 Hz to 3 kHz
Tone Type	(8) selectable
Touch to Acknowledge	No
Number of Alarms	8
Voltage Rating	12-48 VDC
Mounting	Surface
IP Rating	IP66
NEMA Rating	4/4X

Agency Approvals

UL Listed File #	S7256
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/21556818055.pdf>
See store item page for other formats.