

# 21565154055 Cut Sheet



Pfannenberg PYRA series Xenon tube audible-visual signal beacon, 103 dB at 1m, (8) selectable tone(s), selectable flashing strobe, amber, 216 x 144 x 172mm, 115 VAC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21565154055>

## Technical Specifications

<b>Brand</b>	Pfannenberg	<b>Material</b>	ABS plastic
<b>Item</b>	Audible-visual signal beacon	<b>Loudness Decibel</b>	103 dB at 1m
<b>Series</b>	PYRA	<b>Tone Frequency</b>	110 Hz to 3 kHz
<b>Bulb Type</b>	Xenon tube	<b>Tone Type</b>	(8) selectable
<b>Operator Size</b>	216 x 144 x 172mm	<b>Touch to Acknowledge</b>	No
<b>Operator Color</b>	Amber	<b>Voltage Rating</b>	115 VAC
<b>Light Color(s)</b>	Amber	<b>Mounting</b>	Surface
<b>Light Function</b>	Selectable flashing strobe	<b>IP Rating</b>	IP66
<b>Housing Material</b>	Polycarbonate	<b>NEMA Rating</b>	4/4X

## Agency Approvals

<b>UL Listed File #</b>	S7256
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/21565154055.pdf>  
See store item page for other formats.