

21WN6K1E250-10T5-A Cut Sheet



ODE potable water solenoid valve, 2-port (2-way), 2-position, N.C., lead-free brass body, 1in female NPT inlet(s), 1in female NPT outlet(s), Cv=14, 120 VAC (60Hz)/110 VAC (50Hz) operating voltage, 15 VA.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21WN6K1E250-10T5-A>

Technical Specifications

Brand	ODE
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid slow close
Body Material	Lead-free brass
Inlet Port	1in female NPT
Outlet Port	1in female NPT

Manual Override Type	Locking
Flow Coefficient	14
Minimum Operating Pressure	2.9 psi
Maximum Operating Pressure	232 psi
Operating Voltage	120 VAC (60Hz)/110 VAC (50Hz)
Power Rating	15 VA
Electrical Connection	18mm DIN style wiring plug
Form Factor	Standard
Additional Information	Valve part number: 21WN6K1E250-10T5, coil part number: BDV08110AY

Agency Approvals

UL Listed File #	MH49108
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/21WN6K1E250-10T5-A.pdf>
See store item page for other formats.