


# 2200-8M-20-NG Cut Sheet



SureMotion timing belt, 8mm 8M pitch, 20mm wide, 275 tooth, 2200mm pitch length (circumference), neoprene, fiberglass reinforced.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2200-8M-20-NG>

## Technical Specifications

|                            |             |
|----------------------------|-------------|
| <b>Brand</b>               | SureMotion  |
| <b>Item</b>                | Timing belt |
| <b>Pitch</b>               | 8mm 8M      |
| <b>Width</b>               | 20mm        |
| <b>Number of Teeth</b>     | 275         |
| <b>Pitch length</b>        | 2200mm      |
| <b>Material</b>            | Neoprene    |
| <b>Reinforcement</b>       | Fiberglass  |
| <b>Belt Tensile Rating</b> | 2023lb      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |