

# 22003001 Cut Sheet



Socomec SIRCO M series rotary disconnect switch, load break capable, 3-pole, 600 VAC, 20A, 65kA SCCR, DIN rail or panel mount, UL 508 rated, front or side operated, accepts 5 x 5mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22003001>

## Technical Specifications

Brand	Socomec	SCCR Rating	65kA SCCR
Item	Disconnect switch	Mounting	DIN rail or panel
Series	SIRCO M	UL Rating	UL 508 rated
Fusible	No	Configuration	Front or side operated
Load Break Capable	Yes	Shaft Size	Accepts 5 x 5mm size shaft
Number of Poles	3	Handle Type	Rotary
Voltage Rating	600 VAC	Additional Information	Purchase handle separately. Line and load terminal shrouds sold separately. Suitable as motor disconnect
Amperage Rating	20A		

## Agency Approvals

UL Listed File #	E173959
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	2186005
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/22003001.pdf>  
See store item page for other formats.