

22003010 Cut Sheet



Socomec SIRCO M Compact series rotary disconnect switch, load break capable, 3-pole, 600 VAC, 100A, 100kA SCCR, DIN rail or panel mount, UL 98 rated, front or side operated, accepts 5 x 5mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22003010>

Technical Specifications

Brand	Socomec
Item	Disconnect switch
Series	SIRCO M Compact
Fusible	No
Load Break Capable	Yes
Number of Poles	3
Voltage Rating	600 VAC
Amperage Rating	100A
SCCR Rating	100kA SCCR
Mounting	DIN rail or panel
UL Rating	UL 98 rated
Configuration	Front or side operated
Shaft Size	Accepts 5 x 5mm size shaft
Handle Type	Rotary
Additional Information	Purchase handle separately. Line and load terminal shrouds sold separately. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E201138
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	2316514
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document