

22052 Cut Sheet



Murrelektronik universal surge suppressor, resistor-capacitor, 127-240 VAC/VDC, 1-phase, 0-60Hz, 15W, pigtail with spade connectors, contactor mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22052>

Technical Specifications

Brand	Murrelektronik
Application	Universal
Item	Surge suppressor
Circuit Type	Resistor-capacitor
Voltage Rating	127-240 VAC/VDC
Number of Phases	1
Frequency	0-60Hz
Power Rating	15W
Connection	Pigtail with spade connectors
Mounting	Contactor
Additional Information	Pigtail for non-contactor applications

Agency Approvals

UL Listed File #	None
UL Recognized File #	E140415
UL Hazardous File #	None
CE	View CE declarations
CSA File #	080128_0_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/22052.pdf>
See store item page for other formats.