

221-413 Cut Sheet



WAGO 221 series splicing connector, lever, side-entry, 3 openings, copper conductor, 24-12 AWG solid, 24-12 AWG stranded, 20A, 600V, polycarbonate housing, transparent/orange. Package of 50.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/221-413>

Technical Specifications

Brand	WAGO
Series	221
Item	Connector
Connector Type	Splicing
Splice Type	Lever
Wiring Direction	Side-entry
Number Of Openings	3
Conductor Material (PF)	Copper

Solid Conductor Size	24-12 AWG
Stranded Conductor Size	24-12 AWG
Amperage Rating	20A
Voltage Rating	600V
Housing Material	Polycarbonate
Housing Color	Transparent/orange
Quantity per Pack	50

Agency Approvals

UL Listed File #	E69654, E201573
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/221-413.pdf>
See store item page for other formats.