

221-415/K006-0000 Cut Sheet



WAGO 221 series splicing connector, lever, side-entry, 5 openings, copper conductor, 24–12 AWG solid, 24–12 AWG stranded, 20A, 600V, polycarbonate housing, transparent/orange. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/221-415/K006-0000>

Technical Specifications

Brand	WAGO	Solid Conductor Size	24–12 AWG
Series	221	Stranded Conductor Size	24–12 AWG
Item	Connector	Amperage Rating	20A
Connector Type	Splicing	Voltage Rating	600V
Splice Type	Lever	Housing Material	Polycarbonate
Wiring Direction	Side-entry	Housing Color	Transparent/orange
Number Of Openings	5	Quantity per Pack	10
Conductor Material (PF)	Copper		

Agency Approvals

UL Listed File #	E201573, E69654
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/221-415_K006-0000.pdf
See store item page for other formats.