

221-415 Cut Sheet



WAGO 221 series splicing connector, lever, side-entry, 5 openings, copper conductor, 24-12 AWG solid, 24-12 AWG stranded, 20A, 600V, polycarbonate housing, transparent/orange. Package of 25.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/221-415>

Technical Specifications

| | |
|--------------------------------|------------|
| Brand | WAGO |
| Series | 221 |
| Item | Connector |
| Connector Type | Splicing |
| Splice Type | Lever |
| Wiring Direction | Side-entry |
| Number Of Openings | 5 |
| Conductor Material (PF) | Copper |

| | |
|--------------------------------|--------------------|
| Solid Conductor Size | 24-12 AWG |
| Stranded Conductor Size | 24-12 AWG |
| Amperage Rating | 20A |
| Voltage Rating | 600V |
| Housing Material | Polycarbonate |
| Housing Color | Transparent/orange |
| Quantity per Pack | 25 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E69654, E201573 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/221-415.pdf>
See store item page for other formats.