

22143503 Cut Sheet



Socomec SIRCO M series rotary enclosed disconnect switch, load break capable, 3-pole, 600 VAC, 30A, 65kA SCCR, wall mount, UL 508 rated, 3.9 x 6.38 x 4.37in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22143503>

Technical Specifications

Brand	Socomec
Item	Enclosed disconnect switch
Series	SIRCO M
Fusible	No
Load Break Capable	Yes
Number of Poles	3
Voltage Rating	600 VAC
Amperage Rating	30A
SCCR Rating	65kA SCCR
Mounting	Wall
UL Rating	UL 508 rated
Handle Type	Rotary
Housing Size	3.9 x 6.38 x 4.37in
Additional Information	Lockout/tagout capable. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E173959
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document