

# 22243506 Cut Sheet



Socomec SIRCO M series rotary enclosed disconnect switch, load break capable, 3-pole, 600 VAC, 60A, 50kA SCCR, wall mount, UL 508 rated, 4.94 x 8.27 x 4.37in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22243506>

## Technical Specifications

|                        |  |
|------------------------|--|
| Brand                  | Socomec  |
| Item                   | Enclosed disconnect switch                           |
| Series                 | SIRCO M  |
| Fusible                | No   |
| Load Break Capable     | Yes  |
| Number of Poles        | 3  |
| Voltage Rating         | 600 VAC  |
| Amperage Rating        | 60A  |
| SCCR Rating            | 50kA SCCR  |
| Mounting               | Wall   |
| UL Rating              | UL 508 rated   |
| Handle Type            | Rotary   |
| Housing Size           | 4.94 x 8.27 x 4.37in                                 |
| Additional Information | Lockout/tagout capable. Suitable as motor disconnect |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E173959                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/22243506.pdf>  
See store item page for other formats.