

# 22613 Cut Sheet



Viking mechanic-length drill bit, 1/8in, step point point, high-speed steel (HSS), black and gold oxide finish, round shank, 2.5in (64mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22613>

## Technical Specifications

<b>Brand</b>	Viking	<b>Point Angle</b>	135 degrees
<b>Item</b>	Drill bit	<b>Point Cut</b>	Step point
<b>Replacement</b>	No	<b>Shank Type</b>	Round
<b>Drill Bit Type</b>	Mechanic-length	<b>Overall Length</b>	2.5in (64mm)
<b>Size</b>	1/8in	<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron
<b>Material</b>	High-speed steel (HSS)	<b>Application</b>	Hole cutting
<b>Finish</b>	Black and gold oxide	<b>Quantity per Pack</b>	5
<b>Flute Length</b>	1-5/8in		

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>