

# 22633 Cut Sheet

Viking mechanic-length drill bit, 5/32in, step point point, high-speed steel (HSS), black and gold oxide finish, round shank, 2.8in (71mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22633>

## Technical Specifications

Brand	Viking
Item	Drill bit
Replacement	No
Drill Bit Type	Mechanic-length
Size	5/32in
Material	High-speed steel (HSS)
Finish	Black and gold oxide
Flute Length	2in

Point Angle	135 degrees
Point Cut	Step point
Shank Type	Round
Overall Length	2.8in (71mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting
Quantity per Pack	5

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>