

# 22653 Cut Sheet

Viking mechanic-length drill bit, 3/16in, step point point, high-speed steel (HSS), black and gold oxide finish, 3-flat shank, 3in (76mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22653>



## Technical Specifications

Brand	Viking	Point Angle	135 degrees
Item	Drill bit	Point Cut	Step point
Replacement	No	Shank Type	3-flat
Drill Bit Type	Mechanic-length	Overall Length	3in (76mm)
Size	3/16in	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Material	High-speed steel (HSS)	Application	Hole cutting
Finish	Black and gold oxide	Quantity per Pack	5
Flute Length	2-5/16in		

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>