

22673 Cut Sheet

Viking mechanic-length drill bit, 7/32in, step point point, high-speed steel (HSS), black and gold oxide finish, 3-flat shank, 3.3in (84mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22673>

Technical Specifications

Brand	Viking
Item	Drill bit
Replacement	No
Drill Bit Type	Mechanic-length
Size	7/32in
Material	High-speed steel (HSS)
Finish	Black and gold oxide
Flute Length	2-1/2in

Point Angle	135 degrees
Point Cut	Step point
Shank Type	3-flat
Overall Length	3.3in (84mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting
Quantity per Pack	5

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement