

# 22733 Cut Sheet

Viking mechanic-length drill bit, 5/16in, step point point, high-speed steel (HSS), black and gold oxide finish, 3-flat shank, 4in (102mm) overall length. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22733>

## Technical Specifications

Brand	Viking
Item	Drill bit
Replacement	No
Drill Bit Type	Mechanic-length
Size	5/16in
Material	High-speed steel (HSS)
Finish	Black and gold oxide
Flute Length	3-3/16in

Point Angle	135 degrees
Point Cut	Step point
Shank Type	3-flat
Overall Length	4in (102mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting
Quantity per Pack	2

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>