

# 22753 Cut Sheet



Viking mechanic-length drill bit, 11/32in, step point point, high-speed steel (HSS), black and gold oxide finish, 3-flat shank, 4.1in (104mm) overall length. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22753>

## Technical Specifications

Brand	Viking
Item	Drill bit
Replacement	No
Drill Bit Type	Mechanic-length
Size	11/32in
Material	High-speed steel (HSS)
Finish	Black and gold oxide
Flute Length	3-7/16in

Point Angle	135 degrees
Point Cut	Step point
Shank Type	3-flat
Overall Length	4.1in (104mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting
Quantity per Pack	2

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>