

22873 Cut Sheet



Viking mechanic-length drill bit set, 15 pieces, high-speed steel (HSS), 3-flat shank, imperial, gold oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22873>

Technical Specifications

Brand	Viking	Shank Type	3-flat
Item	Drill bit set	Application	Hole cutting
Number of Pieces	15	For Use On	Stainless steel, steel, sheet metal, brass and acrylic
Material	High-speed steel (HSS)	Measurement Type	Imperial
Drill Bit Type	Mechanic-length	Package Type	Metal index case
Drill Bit Size	1/16in, 3/32in, 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in and 1/2in	Set Includes	Includes (15) mechanic length step point drill bits (1/16in, 3/32in, 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in), durable metal case
Finish	Gold oxide		
Point Angle	135 degrees		
Point Cut	Step point		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement