

228 Cut Sheet



Minerallac 2-hole conduit mount strap, standard duty, UL Type UL 1565. Package of 100. For use with 3/8in LFMC, 1/2in EMT, 6 AWG.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/228>

Technical Specifications

Brand	Minerallac
Item	Strap
Mount Type	Conduit mount
Mounting Holes	2-hole
Mounting Hole Size	3/16in
Duty Rating	Standard duty
Material	Steel
Finish	Pre-galvanized
Outside Diameter	0.70-0.79in

Rigid Metallic Conduit (RMC) Trade Size	3/8in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	3/8in
Service Entrance Wire (SER) Size	6 AWG
UL Type	UL 1565
Quantity per Pack	100
For Use With	3/8in LFMC, 1/2in EMT, 6 AWG

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document