

22903 Cut Sheet



Viking mechanic-length drill bit set, 29 pieces, high-speed steel (HSS), 3-flat shank, imperial, gold oxide finish, ultra-dex carrying case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22903>

Technical Specifications

Brand	Viking
Item	Drill bit set
Number of Pieces	29
Material	High-speed steel (HSS)
Drill Bit Type	Mechanic-length
Drill Bit Size	1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in and 1/2in
Finish	Gold oxide
Point Angle	135 degrees
Point Cut	Step point

Shank Type	3-flat
Application	Hole cutting
For Use On	Stainless steel, steel, sheet metal, brass and acrylic
Measurement Type	Imperial
Package Type	Ultra-dex carrying case
Set Includes	Includes (29) mechanic length step point drill bits (1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in, 1/2in), ultra-dex carrying case

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement