

23070T Cut Sheet



Southwire MaintenancePRO autoranging clamp meter, True RMS AC/DC voltage, AC/DC current, resistance, continuity, capacitance and frequency, CAT IV 600V/CAT III 1000V. Test leads included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23070T>

Technical Specifications

Brand	Southwire
Item	Clamp meter
Series	MaintenancePRO
Safety Rating	CAT IV 600V/CAT III 1000V
AC Voltage Range	(Autoranging), 0-6.000 VAC, 0-60.00 VAC, 0-600.0 VAC and 0-1000 VAC
DC Voltage Range	(Autoranging), 0-600.0 mVDC, 0-6.000 VDC, 0-60.00 VDC, 0-600.0 VDC and 0-1000 VDC
AC Current Range	0-600A and 0-1000A
DC Current Range	0-600A and 0-1000A
Resistance Range	(Autoranging), 0-600.0 ohm, 0-6.000 kohm, 0-60.00 kohm, 0-600.0 kohm, 0-6.000 Mohm and 0-60.00 Mohm
Capacitance Range	(Autoranging), 0-60.00 nF, 0-600.0 nF, 0-6.000 µF, 0-60.00 µF, 0-600.0 µF and 0-6000 µF
Frequency Range	(Autoranging), 0-6.000 Hz, 0-60.00 Hz, 0-600.0 Hz, 0-6.000 kHz, 0-60.00 kHz, 0-600.0 kHz and 0-10.00 Mhz
Non-contact AC Voltage Detection	100-1000 VAC
Temperature Range	-4 degrees F to 1400 degrees F and -20 degrees C to 780 degrees C
Includes	Test leads
Application	Electrical testing and continuity testing

Agency Approvals

UL Listed File #	E361819
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	No
EU REACH	View EU REACH document