

# 231014NPT Cut Sheet

RUKO hand tap, 1/4-18 NPT, square shank per DIN 10, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/231014NPT>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Hand tap
<b>Thread</b>	1/4-18 NPT per ANSI/ASME B1.20.1
<b>Thread Length</b>	0.98in
<b>Overall Length</b>	2.8in (71mm)
<b>Tap Drill Size</b>	7/16in
<b>Shank</b>	Square shank per DIN 10
<b>Material</b>	High-speed steel (HSS)
<b>Finish</b>	Bright
<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron
<b>Application</b>	Thread making

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>