

# 231116NPT Cut Sheet



RUKO hand tap, 1/16-27 NPT, square shank per DIN 10, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/231116NPT>

## Technical Specifications

Brand	RUKO
Item	Hand tap
Thread	1/16-27 NPT per ANSI/ASME B1.20.1
Thread Length	0.75in
Overall Length	2.6in (66mm)
Tap Drill Size	Letter size D
Shank	Square shank per DIN 10
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Thread making

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>